



NON-TOXIC STEEL SPIRAL PVC


ORDER REF: BWR-SIZE MM

CONSTRUCTION : STRONG VERY FLEXIBLE AND SMOOTH NON-TOXIC, TRANSPARENT PLASTICIZED PVC, SHOCK RESISTANT GALVANISED SPIRAL ABRASION AND WEATHER RESISTANT, SMOOTH OUTSIDE

REINFORCEMENT : GALVANISED STEEL WIRE HELIX

APPLICATION : FOR SUCTION AND DELIVERY OF WATER, MINERAL WATER, FRUIT JUICES, LIQUIDS

ID		BP	VACUUM	BR	W/A	COIL
inch	mm	BAR	m.H ² O	mm	gr/m	m
5/16	8	21	9	20	135	30/10
3/8	10	21	9	20	160	30/10
1/2	12	21	9	25	180	30/10
5/8	16	18	9	35	225	30/10
3/4	20	15	9	50	340	30/10
1	25	15	9	60	510	30/10
1 1/4	32	13	9	75	650	30/10
1 1/2	38	12	9	90	800	30/10
	40	9	9	95	870	30/10
	45	9	8	125	1200	30/10
2	51	9	8	125	1200	30/10
	60	7	7	135	1800	30/10
2 1/2	63	7	7	150	1950	30/10
3	76	6	6	195	2500	30/10
4	102	6	6	300	3400	30/10



-5°C to +60°C

BRANDING: BOSPHORUS - NON TOXIC SIZE (MM)

COLOUR: CLEAR

EEC DIRECTIVE:90/138