

## COTTON OVERBRAIDED FUEL DIN 73379 TYPE B



ORDER REF: CFH-SIZE MM

**TUBE** : FUEL AND OIL RESISTANT, SMOOTH SYNTHETIC NITRILE BLACK RUBBER


**COVER** : SINGLE TEXTILE BRAID

**APPLICATION** : FOR DELIVERY OF TRANSMISSION OIL, FUEL OIL, AUTOMOTIVE GASOLINE ETC

**SPECIFICATION** : DIN 73379 TYPE B

OTHER DIAMETERS AVAILABLE UPON REQUEST

ID		OD	WP	WP	W/A	COIL
inch	mm	mm	BAR	PSI	gr/m	m
	3.2	7.0	10	145	38	20
	3.5	7.5	10	145	45	20
	4.0	9.0	10	145	63	20
	4.5	9.5	10	145	72	20
	5.0	10.0	10	145	76	20
	5.5	10.5	10	145	81	20
	6.0	11.0	10	145	90	20
	7.0	12.0	10	145	95	20
	7.5	12.5	10	145	101	20
	8.0	13.0	10	145	106	20
	9.0	14.0	10	145	117	20
	10.0	15.0	10	145	132	20
	12.0	18.0	10	145	150	20



-40°C to +85°C

BRANDING: DIN73379 TYPE B

COLOUR: BLACK