




GREEN MEDIUM DUTY SUCTION & DELIVERY

ORDER REF: GMD-SIZE MM

- CONSTRUCTION** : STRONG, FLEXIBLE AND SMOOTH PLASTICIZED PVC, SHOCK & CRUSH RESISTANT, LIGHT CORRUGATED OUTSIDE
- REINFORCEMENT** : SHOCK RESISTANT PVC SPIRAL
- APPLICATION** : FOR MEDIUM DUTY SUCTION AND DELIVERY OF WATER, SALT WATER, LIGHT CHEMICALS, LIQUIDS IN AGRICULTURAL INDUSTRIAL APPLICATIONS AND CONSTRUCTION

ID		BP	VACUUM	BR	W/A	COIL
inch	mm	BAR	m.H ² O	mm	gr/m	m
1	25	27	8	140	480	10/20/30/50
1 1/4	32	24	8	150	580	10/20/30/50
1 1/2	38	24	8	180	670	10/30/50
2	51	21	8	220	975	6/10/20/30/50
2 1/2	63	20	8	260	1350	10/30
3	76	18	8	320	1700	6/10/20/30
4	102	14	7	400	2600	6/10/20/30
5	127	12	7	600	3650	30
6	152	9	7	800	5100	6/10/20/30
8	203	8	6	1250	7850	6

STRAIGHT CURED LENGTHS AVAILABLE IN 4" and 6"



-5°C to +60°C

BRANDING: MEDUSA MD (SIZE MM)

COLOUR: GREEN