




## PREMIUM ORANGE LPG 20 BAR

ORDER REF: RPO-SIZE MM

- TUBE** : BLACK, LPG AND RESISTANT SPECIAL SYNTHETIC RUBBER  
**REINFORCEMENT** : HIGH TENSILE SYNTHETIC TEXTILE  
**COVER** : ABRASION, FLAME, OZONE AND WEATHER RESISTANT, ORANGE COLOUR SMOOTH SYNTHETIC RUBBER  
**APPLICATION** : FOR LIQUID PROPANE GAS APPLICATIONS  
**SPECIFICATION** : EN 559 - ISO3821

ID		OD		WP		BP		BR		W/A		COIL	
inch	mm	mm	BAR	PSI	BAR	PSI	mm	gr/mt	mt				
1/4	6	13	20	300	60	900	60	192	100				
5/16	8	15	20	300	60	900	80	230	100				
3/8	10	18	20	300	60	900	100	268	100				
1/2	12.7	22.5	20	300	60	900	127	415	100				
3/4	19	30	20	300	60	900	190	520	50				



-25°C to +110°C

BRANDING: URANUS - LPG - W.P. 20 BAR  
EN 559/ISO 3821 (SIZE MM)

COLOUR: ORANGE