

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19160-0041](#)
Status: **Active**
Overview: [Splices](#)
Description: Twist Lock Splice for 14-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)

Agency Certification

CSA LR700095
 UL E32244

General

Product Family Splices
 Series [19160](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 MolexKits Yes
 Overview [Splices](#)
 Product Name Closed-End Twist Lock
 UPC 800753110458

Physical

Barrel Type Closed
 Color - Resin Orange
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 1.341/g
 Packaging Type Bag
 Temperature Range - Operating 105°C
 Wire Insulation Diameter 9.91mm max.
 Wire Size AWG 14, 16, 18, 20, 22
 Wire Size mm² 0.35 - 2.00

Electrical


Voltage - Maximum 600V

Material Info

Old Part Number TL-O

Reference - Drawing Numbers

Product Specification PS-19902-013
 Sales Drawing SD-19160-005



EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19160Series](#)