

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0067](#)
Status: **Active**
Overview: Mini-Fit Jr.™ Power Connectors
Description: Mini-Fit® Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel

Documents:

Drawing (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-5556-002 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-5558-001 (PDF)	

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800754394024

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.120/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical


Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5558-PBT2
-----------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-5556-002
Sales Drawing	SD-5558****
Test Summary	TS-5556-002



EU RoHS

**ELV and RoHS
Compliant**

**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[5558Series](#)

Mates With

[5556](#) Mini-Fit® Crimp Terminal

Use With

[5559](#) Mini-Fit Jr.™ Plug Housing, [30068](#)
 Mini-Fit® TPA Plug Housing, [42475](#) Mini-
 Fit® BMI Plug Housing

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
--------------------	------------------

FineAdjust™ Applicator for Insulation OD 1.10-1.30mm - 22-28 AWG	0639020200
--	----------------------------

FineAdjust™ Applicator for Insulation OD 1.30-1.50mm - 22-28 AWG	<u>0639002700</u>
FineAdjust™ Applicator for Insulation OD 0.95-1.08mm - 22-28 AWG	<u>0639023800</u>
Hand Crimp Tool for Crimp Terminals	<u>0638191000</u>
T2 Terminator™ for insulation OD 0.95-1.08mm - 22-28 AWG	<u>0639123800</u>
T2 Terminator™ for insulation OD 1.30-1.50mm - 22-28 AWG	<u>0639102700</u>
T2 Terminator™ for insulation OD 1.10-1.30mm - 22-28 AWG	<u>0639120200</u>
Extraction Tool	<u>0011030044</u>
Japan	
Description	Product #
Applicator for M21 1A Bench Press, 22-28 AWG Wire	<u>0570383000</u>

This document was generated on 10/28/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION