


MECHANICAL DETAILS

- Shell Style Model** EG* : Fixed receptacle nut fixing
- Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
- Housing Material** Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
- Cable Fixing** 0 - 0 mm
- Variant 2** :

| | | E | L | M | N | S1 | S3 |
|-----|--|------|------|------|------|------|------|
| Mm. | | 9 | 30.7 | 5 | 28.6 | 18.5 | 24 |
| In. | | 0.35 | 1.21 | 0.20 | 1.13 | 0.73 | 0.94 |



PERFORMANCE DETAIL

- Insert** 2K.326 : 26 Low Voltage
- Insulator** L: PEEK
- Specifications**
- Contact Type:** Solder



OTHER CHARACTERISTICS







- Endurance (Shell)** Endurance (Shell):
- Temp (min)** -55°C
- Temp (max)** +200°C
- Humidity (max):** <=95% [at 60 deg C /140 F]
- Vibration:** 15 g [10 Hz - 2000 Hz]
- Shock Resistance:** 100 g [6 ms]
- Salt Spray** >144 hr
- Climatical** 50/175/21
- Shielding (min):** 95 dB (10 MHz)
- Shielding (min):** 80 dB (1 GHz)
- IP Rating** 68



Available Download

 [unipole_multipole.pdf](#)

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)