



### Main

Commercial Status	Commercialised
Range of product	Zelio Relay
Product or component type	Solid state relay
Device short name	SSM
Number of channels	1
Network number of phases	1 phase

### Complementary

Mounting support	Symmetrical DIN rail
[In] rated current	6 A
Output voltage	24...280 V AC
Control circuit voltage	200...265 V AC
Contacts type and composition	1 NO
Tightening torque	0.5...0.8 N.m for output 0.5...0.8 N.m for input
Connections - terminals	Screw terminals 1 x 0.3...1 x 2.5 mm <sup>2</sup> for output - AWG 22...AWG 14 Screw terminals 1 x 0.3...1 x 1.5 mm <sup>2</sup> for input - AWG 22...AWG 16
Capacitance unbalance	<= 10 pF for input/output
Insulation resistance	1000 MOhm at 500 V DC
Local signalling	LED green for input status
Switching voltage	<= 90 V AC turn-off >= 200 V AC turn-on
Input current limits	2.5...3.5 mA
Solid state output type	Zero voltage switching SCR output
Load current	0.00015...6 A
Absolute maximum voltage	600 V
Surge current	<= 300 A for 20 ms <= 285 A for 16.6 ms
Voltage drop	<= 1.3 V on-state
Motor power hp	0.16 hp at 40 °C 240 V AC
Maximum I <sup>2</sup> t for fusing	375 A <sup>2</sup> .s for 8.33 ms at 60 Hz half cycle 410 A <sup>2</sup> .s for 10 ms at 50 Hz half cycle
Leakage current	<= 0.1 mA off-state
DV/Dt	500 V/μs off-state at maximum voltage
Response time	30 ms turn-off 0.5 cycle turn-on

Cos phi	>= 0.5 with maximum load
Overvoltage category	III
Width	11 mm
Height	90.3 mm
Depth	83.7 mm
Product weight	0.05 kg



## Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	4 kV AC for input or output to case 4 kV AC for input/output
Pollution degree	2
Standards	IEC 61000 IEC 60950-1 IEC 62314
Product certifications	CSA RoHS UL REACH
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-30...80 °C
Ambient air temperature for storage	-30...100 °C


## Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	00785901864783
Nbr. of units in pkg.	1
Package weight(Lbs)	0.11
Returnability	N
Country of origin	MX


## Offer Sustainability

Sustainable offer status	Green Premium product
RECh	Reference not containing SVHC above the threshold
Product environmental profile	Available  <a href="#">Download Product Environmental</a>
Product end of life instructions	Available  <a href="#">Download End Of Life Manual</a>

Dimensions



Derating Curves



- A : Load Current (Amperes)
- B : Ambient Temperature (°C)
- 1 : Multiple units, no minimum spacing between components
- 2 : Installed single unit, distance to adjacent components more than 11 mm