

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **504622-2410**
Status: **Active**
Overview: SlimStack™ 0.35mm pitch Board-to-Board Connectors
Description: 0.35mm Pitch SlimStack™ SSB6 Board-to-Board Plug Connector, Surface Mount, Dual Row, Vertical, 0.60mm Stacking Height, 2.00mm Width, 24 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-504618-001 \(PDF\)](#)

General

Product Family	PCB Headers
Series	<u>504622</u>
Application	Board-to-Board
Overview	<u>SlimStack™ 0.35mm pitch Board-to-Board Connectors</u>
Product Name	SlimStack™
UPC	887191621319

Physical

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Compliant	No
Mated Height	0.60mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	6.610/mg
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.35mm
Polarized to Mating Part	No
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount


Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-504618-001
Sales Drawing	SD-504622-001, SD-504622-002



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
 504622Series

Mates With
 504618 0.35mm Pitch SlimStack™ SSB6 Board-to-Board Receptacle