

## MECHANICAL DETAILS

**Shell Style Model** ERA\* : Fixed receptacle nut fixing


**Keying** Circular (can rotate), plug has male contact(s)

**Housing Material** Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

**Cable Fixing** 0 - 0 mm

**Variant 2** :

			A	B	E	L	M	S1
Mm.			10	12.4	7	17.5	1.2	8.2
In.			0.39	0.49	0.28	0.69	0.05	0.32



## PERFORMANCE DETAIL

**Insert** 0S.116 : 1 Low Voltage

**Insulator** L: PEEK

**Specifications**

**Contact Type:** Solder



## OTHER CHARACTERISTICS

**Endurance (Shell)** Endurance (Shell):

**Temp (min)** -55°C

**Temp (max)** +250°C

**Humidity (max):** <=95% [at 60 deg C /140 F]

**Vibration:** 15 g [10 Hz - 2000 Hz]

**Shock Resistance:** 100 g [ 6 ms]

**Salt Spray** >144 hr

**Climatical** 50/175/21

**Shielding (min):** 75 dB (10 MHz)

**Shielding (min):** 40 dB (1 GHz)







**IP Rating** 50



## Available Download

 [unipole\\_multipole.pdf](#)

## Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)