


MECHANICAL DETAILS

Shell Style Model	ERA* : Fixed receptacle nut fixing
Keying	Circular (can rotate), plug has male contact(s)
Housing Material	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
Cable Fixing	0 - 0 mm

Variant 2 :

		A	B	E	L	M	S1
Mm.		14	16	7.5	20.2	1.5	10.5
In.		0.55	0.63	0.30	0.80	0.06	0.41



PERFORMANCE DETAIL

Insert	1S.275 : 1 Coax (75 Ohm)
Insulator	T: PTFE
Specifications	
Contact Type:	Coaxial 75 Ohm (Solder)
Max. Matings:	1000
Contact Dia.:	1.3 mm (0.0512in)
Bucket Dia.:	1.1 mm (0.0432in)
Cable type:	A RG



OTHER CHARACTERISTICS







Endurance (Shell)	Endurance (Shell):
Temp (min)	-55°C
Temp (max)	+250°C
Humidity (max):	<=95% [at 60 deg C /140 F]
Vibration:	15 g [10 Hz - 2000 Hz]
Shock Resistance:	100 g [6 ms]
Salt Spray	>144 hr
Climatical	50/175/21
Shielding (min):	75 dB (10 MHz)
Shielding (min):	40 dB (1 GHz)
IP Rating	50



Available Download

 [Coax_triax_mixed_en.pdf](#)

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)