

Item # LP1K1201BD, TeSys K Non-reversing Contactor

TeSys K IEC Contactor - 12A - 24Vdc Coil



Specifications

| | |
|----------------------------------|--|
| Type | TeSys K IEC Contactor - 12A - 24Vdc Coil |
| Termination Method | Screw Clamp |
| Contact Rating | 600V / 12A |
| Coil Voltage | 24Vdc |
| Std. DC Voltage Code | BD |
| Low Consumption DC Voltage Code | N/A |
| Coil Consumption Inrush | 3 W |
| Coil Consumption Sealed | 3W |
| Power Wire Size | #12 - #18 AWG |
| Power Terminal Torque | 7 lb-in (0.8 Nm) |
| Control Wire Size | #12 - #18 AWG |
| Control Terminal Torque | 7 lb-in (0.8 Nm) |
| Mounting Hardware | 35mm DIN Rail, 4mm screw |
| Weight | 0.40 lb (0.18 kg) |
| AC1 Resistive Rating | 20 Amp |
| AC3 Single Phase 115V | 0.5 HP |
| AC3 Single Phase 230V | 1.5 HP |
| AC3 Three Phase 200V | 3 HP |
| AC3 Three Phase 230V | 3 HP |
| AC3 Three Phase 460V | 7.5 HP |
| AC3 Three Phase 575V | 10 HP |
| Control Contact Rating (0NC/1NO) | N/A |

| | |
|---|-----------------|
| Control Contact Rating (1NC/0NO) | A600 |
| UL File/CCN | E164353 / NKCR |
| CSA File | LR43364 3211 03 |
| Meets Standard | IEC 60647-1-1 |
| CE | Yes |
| RoHS | Yes |