



ERN.00.650.GLN

MECHANICAL DETAILS

Shell Style Model ERN* : Fixed receptacle
Single Contact; nut fixing
with grounding tab
PEEK or POM outer shell


Keying Circular (can rotate)

Housing Material PEEK (Polyetheretherketone)
shell and collet nut, nickel plated
brass latch sleeve and mid pieces

Cable Fixing 0 - 0 mm

Variant 2 :

	A	B	E	L1	M	S1	e
Mm.	9	10.3	5.5	15	1	6.3	M7x0.5
In.	0.35	0.41	0.22	0.59	0.04	0.25	



PERFORMANCE DETAIL

Insert 0.65 : 1 Triax (50 Ohm)

Insulator L: PEEK

Specifications

Contact Type: Triaxial 50 Ohm (Printed Circuit Board)

Max. Matings: 1000

Contact Dia.: 0.5 mm (0.02" in)



OTHER CHARACTERISTICS

Shell Style/Model Libellé

IP Rating 50



Available Download

[Coax_triax_mixed_en.pdf](#)

Related links

- [Contact](#)
- [Quote Request](#)
- [Catalogs Downloads](#)
- [Catalogs Requests](#)
- [Sample Request](#)
- [3D drawings](#)