



**Dual-Rated  
T&B Catalog Number:**

ADR11-32  
78378661006  
Active

**UPC Number:  
Status:  
Description:**

Type ADR-ALCUL Three-Conductor, Two-Hole Mount for Conductor Range Max 1/0 Str., Min 14 AWG

**Features**

Easy Installation - no special tools required.

**General**

Style	ALCUL Three-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	1/0 Str.
Conductor Range (AL or CU) Minimum	14 AWG

**Dimension Information**

Length (inches)	2 29/32
Width (inches)	1 15/16
Height (inches)	7/8
D (inches)	11/32
E (inches)	3/8
F (inches)	1/4
G (inches)	2 5/32
I (inches)	45/64

**Packaging**

T&B Inner Pack	6
Package in Units	60
T&B Sold in UOM	Each
T&B Weight Per UOM	22 lbs. per 100

**Application Support**

T&B Sales Drawings	wsd-001273
--------------------	------------

**Notes**

NEMA spacing 1 inch centers.  
Connectors accomodating conductors 600 kcmil and larger have double rows of set screws (D suffix).  
UL 486B tested, AL9CU rated

**Certifications**

RoHS Compliance	No
-----------------	----

**Certifications**



File Nbr:  
E9809