


LOW VOLTAGE SOLDERING IRONS



DATA SHEET

Antex part number: TK2KN60

TC25A



A Low voltage soldering iron from Antex, for use with 660A 690D & 760RWK soldering stations, where a fully controllable temperature output is required.

- 25 watts
- 24 volt with PSU plug and 1.2 meter silicone lead.
- Plated long-life tip supplied
- Replacement tips and elements available separately
- Thermocouple temperature sensing

SPECIFICATIONS TC 50

NOMINAL POWER (W)	25
STANDARD VOLTAGE	24
NOMINAL TIP TEMP (°C)	200-450
FITTED BIT	10 (0.5 mm)
CABLE LENGTH (m)	1.2
CABLE TYPE	SILICONE
LENGTH TIP/HANDLE (mm)	225