

LED Driver - 150W IP67 Waterproof - Constant Voltage Series


A range of compact constant voltage LED drivers capable of providing 150 Watts in a choice of either 12vdc or 24vdc. These LED drivers feature heavy duty input and output and are IP67 rated for use in harsh environments.



Reliable Technical Data

- Rated Input Voltage:100-240VAC
- Input Frequency:50/60Hz
- Output Power:150W
- Dimension:L218xW67xH42mm
- Body:Metal Body By Waterproof Grade IP67
- Open Circuit;Short Circuit;Over Load;
- Over Heat Protection
- Safety According to EN61347-1,EN61347-2-13
- EMI According to EN55015
- EMS According to EN61000-3-2;EN61000-3-3;EN61547
- Approbation Mark:CE ROHS;TUV

Dimension in mm



Characteristics

Rated input voltage: AC200-240V 50Hz (power factor measured at AC230V and full load)

Model No.	Constant out voltage	Load	Max output Current	PF	Ta	Tc	LxWxH	Approval
LED-DR-12V-150W	12V	0-150W	12.5A	0.9	45°C	85°C	219X67X42	TUV
LED-DR-24V-150W	24V	0-150W	6.25A	0.9	45°C	85°C	219X67X42	TUV

PowerPax Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice