


BK

Mobile helpers



Technical data

Electrical data

Nominal wattage	0.23 W
Nominal voltage	4.5 V

Photometrical data

Color temperature	7000 K
-------------------	--------

Dimensions & weight

Length	67.0 mm
Width	67.0 mm
Height	22.0 mm
Diameter	67.0 mm

Colors & materials

Product color	Black
Body material	Aluminum
Cover material	Plastic

Temperatures

Ambient temperature range	0...+25 °C
---------------------------	------------

Additional product data

Lamp designation according to LBS	LED
Equipped with lamp	Yes
Equipment	LED
Light source included	Yes

Capabilities

Type of installation	Surface-mounted
Accessories	Adhesive foil / Magnet / Hook / Loop pads / Velcro / Battery 3x 1.5 V MICRO LR3 AAA
Dimmable	No

Certificates & standards

Standards	CE
Protection class	III

Product datasheet

Type of protection	IP20
--------------------	------

Country specific categorizations

Order number	OTD11403B1
--------------	------------

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321930521	OSRDOTCLPBBLI	-	-	-

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321302847	DOT-it CLASSIC BK	Shipping carton box 6	130 mm x 65 mm x 286 mm	2.42 dm ³	661.00 g
4008321930538	DOT-it CLASSIC BK	Shipping carton box 6	67 mm x 137 mm x 286 mm	2.63 dm ³	661.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.