

## Desktop Labelling machine



It saves you time. It makes life easy. It gives you all the design options you could possibly think of. It even has special features such as a multifunction cutter. When it comes to choice, the PT-3600's really is the ultimate.

### Key Features

- Save time up to 20mm per second
- 6, 9, 12, 18, 24 and 36mm wide durable labels available
- Standalone and PC Connectable
- Convenient built-in automatic cutter
- Easy to use QWERTY keyboard
- Easy-to-read LCD screen
- Includes 24mm black on white tape (8m) and AC Adapter

### Supplies

	6 mm	9 mm	12 mm	18 mm	24 mm	36 mm
<b>Standard - 8m</b>						
	TZe-111	TZe-121	TZe-131	TZe-141	TZe-151	TZe-161
			TZe-132			
			TZe-133			
			TZe-135	TZe-145		
	TZe-211	TZe-221	TZe-231	TZe-241	TZe-251	TZe-261
			TZe-231S*			
		TZe-222	TZe-232	TZe-242	TZe-252	TZe-262
		TZe-223	TZe-233	TZe-243	TZe-253	TZe-263
			TZe-334	TZe-344	TZe-354	
	TZe-315	TZe-325	TZe-335	TZe-345	TZe-355	TZe-365
		TZe-421	TZe-431	TZe-441	TZe-451	TZe-461
			TZe-431S*			
			TZe-435			
		TZe-521	TZe-531	TZe-541	TZe-551	TZe-561
			TZe-535		TZe-555	
	TZe-611	TZe-621	TZe-631	TZe-641	TZe-651	TZe-661
		TZe-721	TZe-731	TZe-741	TZe-751	
<b>Standard - 5m</b>			TZe-B31		TZe-B51	
			TZe-C31		TZe-C51	
<b>Specialty</b>			TZe-M31			
			TZe-MOL35**			
			TZe-MQP35**			
			TZe-MQG35**			
<b>Standard - 8m</b>			TZe-M931		TZe-M951	TZe-M961
<b>Standard</b>						
		TZe-N221	TZe-N231	TZe-N241	TZe-N251	
<b>Standard - 8m</b>						
	TZe-FX211	TZe-FX221	TZe-FX231	TZe-FX241	TZe-FX251	TZe-FX261
	TZe-FX611	TZe-FX621	TZe-FX631	TZe-FX641	TZe-FX651	TZe-FX661
<b>Standard - 8m</b>						
		TZe-S121	TZe-S131	TZe-S141	TZe-S151	
	TZe-S211	TZe-S221	TZe-S231	TZe-S241	TZe-S251	TZe-S261
		TZe-S621	TZe-S631	TZe-S641	TZe-S651	
<b>Standard</b>				TZe-FA3	TZe-FA4B	
<b>Standard - 8m</b>				TZe-SE4		

### Optional Extras

-

## Product Specifications

<b>Housing Colour</b>	Blue and silver
<b>Key Board</b>	QWERTY
<b>Number of Keys</b>	58
<b>Cutter</b>	Yes (automatic)
<b>Power</b>	AC adapter
<b>LCD</b>	20 chrs x 3 line
<b>Print Method</b>	Thermal
<b>Print Head</b>	360dpi
<b>Print Speed</b>	20 mm / sec
<b>Tape Type</b>	TZe
<b>Tape Width</b>	Max. Label width 36mm
<b>Max. Print Width</b>	27mm
<b>Number of Characters</b>	<b>134</b>
<b>Number of Symbols</b>	449
<b>Character Sizes</b>	96 (4 widths x 24 Heights)
<b>Fonts</b>	10 (Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Brunei Bold, Bermuda script, Istanbul and Letter Gothic)
<b>Font Styles</b>	18
<b>Frames</b>	<b>30</b> kinds
<b>Underline</b>	Yes
<b>Strikeout</b>	Yes
<b>Multi-Line</b>	<b>16</b> Lines
<b>Multi-Block</b>	Yes (Max 51 blocks)
<b>Horizontal Alignment</b>	Left (Centre, Right and Just)
<b>Vertical Alignment</b>	PT Editor Software
<b>Tape Length Setting</b>	Yes (60-999mm)
<b>Tape Margin Setting</b>	20-999mm
<b>Memory</b>	10240 characters 100 areas
<b>Barcodes</b>	Yes (9 kinds)
<b>Numbering</b>	Yes
<b>Mirror Printing</b>	Yes
<b>Vertical Printing</b>	Yes
<b>Repeat printing</b>	Yes
<b>Print Preview</b>	Yes
<b>Language Change</b>	-

## Weights/ Dimensions/ Measures

Dimensions

237mm x 302mm x 104mm

Weight

2kg

## What's in the box

24mm Black on White Laminated tape (8M)

AC Adapter

Users Guide

Warranty Card

Tape catalogue