

## Professional Address Label Printer with Wireless



### A professional wired & wireless network label printer.

Brother's QL-720NW offers IT managers a professional, networked label printing solution for a busy office. With wired and wireless networking connections built-in, and the option to create and print labels directly from your iOS or Android device with Brother's free iPrint & Label app, it can be shared widely by everyone in your organisation.

Although compact and easy to use, it's packed full of features to help you produce professional, customised labels. Such as fast print speeds of 93 labels per minute, high print quality of 300 x 600 dpi, easy to change rolls and a suite of free software included to help you integrate with Microsoft Word, Excel, Outlook and your corporate network.

### Key Features

- Save time up to 93 labels per minute print speed
- Durable Automatic cutter
- Share amongst users with wireless and Network connectivity.
- Print from Android and Apple devices with free iPrint&Label app.
- PT-Editor Lite LAN built into device for quick and easy print address labels directly from Microsoft Word, Excel and Outlook
- Space-saving – compact size

### Supplies

#### Die Cut labels

Standard address label (400)	29 x 90mm	DK-11201
Large address label (400)	38 x 90mm	DK-11208
Small address label (400)	29 x 62mm	DK-11209
Shipping label (400)	62 x 100mm	DK-11202
File folder label(400)	17 x 87mm	DK-11203
Multi-purpose label (400)	17 x 54mm	DK-11204
Square label (400)	23 x 23mm	DK-11221
CD/DVD label (400)	58mm	DK-11207
Round Label (400)	12mm	DK-11219
Round Label (400)	24mm	DK-11218

#### Continuous-length labels (30.48 meters)

12mm	DK22214	29mm	DK22210
38mm	DK22225	50mm	DK22223
62mm	DK22205		
54mm	Non Adhesive		DKN55224
62mm	Removable (White)		DK44205
62mm	Removable (Yellow)		DK44605

#### Continuous-length labels (film 15.24 meters)

29mm	DK22211	62mm white	DK22212
62mm Yellow	DK22606	62mm clear	DK22113

### Optional Extras

- None available

## Product Specifications

<b>Housing Colour</b>	Black and White
<b>Key Board</b>	No
<b>Number of Keys</b>	4 (On/Off, Editor Lite, Feed, Cut)
<b>Cutter</b>	Durable Auto cutter (User irreplaceable)
<b>Auto Half Cutter</b>	No
<b>Power</b>	Internal S/W Power Supply
<b>LCD</b>	No
<b>LED</b>	2 (STATUS: 3 colour - Green, Red, Orange / Editor Lite: 1 colour - Green)
<b>Print Method</b>	Thermal
<b>Print Head</b>	300 dpi / 720 dots
<b>Print Speed</b>	150 mm (5.9") / sec / 93 standard address labels / min.
<b>Roll Type</b>	DK rolls (DK Die-cut Labels / DK Continuous Length Tape)
<b>Roll Width</b>	Max. Label width 62mm (2.4")
<b>Max. Print Width</b>	59mm (2.3") max.
<b>Printable Label Length</b>	12.7mm (0.5") - 1m (3')
<b>Printer Driver</b>	QL-720NW
<b>Computer Interface</b>	USB(Full Speed), RS-232C, 10/100 BASE-TX Wired LAN, IEEE802.11b/g/n Wireless LAN,
<b>Network Protocol</b>	Protocol (IPv4) ARP, RARP, BOOTP, DHCP, APIPA (Auto IP), WINS/NetBIOS name resolution, DNS Resolver, mDNS, LLNMR responder, LPR/LPD, Custom Raw Port/Port9100, FTP, Server, TFTP server, SNMPv1/v2c, ICMP
<b>Wireless Security</b>	Wireless SSID (32 chr), WEP 64/128 bit, WPA-PSK (TKIP/AES), WPA2-PSK (AES), LEAP, EAP-FA
<b>Label Editing Software</b>	Win: P-touch Editor ver. 5.0, P-touch Address Book ver. 1.1 Mac: P-touch Editor ver. 5.0
<b>Bar Code</b>	Software side: CODE39, CODE128, UCC/EAN128(GS1-128), ITF(I-2/5), CODABAR(NW-7), UPC-A, UPC-E, EAN13, EAN8, ISBN-2(EAN13 AddOn2), ISBN-5(EAN13 AddOn5), Laser Barcode, POSTNET, RSS(RSS14 Standard, RSS14 Truncated, RSS14 Stacked, RSS14 Stacked Omni, RSS Limited, RSS Expanded, RSS Expanded Stacked), PDF417(Standard, Truncate, Micro), QR code(Model1, Model2, Micro), Data Matrix(ECC Square, ECC Rectangular), MaxiCode(Model2, Model3, Model4, Model5)
<b>Add-in for Microsoft</b>	Win: Word, Outlook, Excel
<b>Database file compatibility</b>	Win: csv, txt, mdb, xls Mac: csv, txt

## Weights/ Dimensions/ Measures

Dimensions

128mm(W) x 236mm(D) x 153mm(H)

Weight

1.2kg (without DK roll)

## What's in the box

CD-ROM (P-touch Editor 5.0 for Windows, P-touch Address Book 1.1, P-touch Editor 5.0 for Mac, Printer Driver, User's Guide, Software User's Guide)  
 Quick Setup Guide, DK Rolls Line-up Guide  
 USB cable, Warranty card  
 DK-11201 Standard Address Labels (100 labels)  
 DK-22205 (62mm Continuous) Starter roll (8 m)  
 Registration Insertion, AC Power cord, EEE insertion

