



KFM LED

KFM LED - Luxo's newest, and most energy-efficient, addition to its growing line of KFM Magnifiers. Now with a dimmable 9W LED lightsource which produces 2500 lux at 12" working distance, it produces nearly 75% greater light output than traditional KFM models.

*Available July 2013



- Lighting: 9W dimmable LED
- Auto shut-off
- Magnification: 3- (1.75X) or 5-diopter (2.25X) lens
- 5" diameter optical quality lens
- 4-diopter and 6-diopter accessory lenses also available
- 30" or 45" internal spring arm
- No knobs to tighten, nothing to adjust - a flexible, self-balancing shade and hands-free neck design allows the lamp head to be secured in any position
- ESD-Safe Magnifiers designed for use in static-sensitive environments are also available.
- Edge clamp or weighted base
- Colors: White, Light Grey or Black (ESD-Safe)
- 5 year warranty

KFM LED

CODES

ESD-SAFE, KFM LED

Article Number	Light Source	Watt	Arm Length	Mount	Diopter Colors
18313BK	LED	9W	45.0/1143	Edge Clamp	5 ■

KFM LED

Article Number	Light Source	Watt	Arm Length	Mount	Diopter Colors
18113BK	LED	9W	45.0/1143	Edge Clamp	3 ■
18113LG	LED	9W	45.0/1143	Edge Clamp	3 ■
18115BK	LED	9W	45.0/1143	Edge Clamp	5 ■
18115LG	LED	9W	45.0/1143	Edge Clamp	5 ■
18115WT	LED	9W	45.0/1143	Edge Clamp	5 ■
18213LG	LED	9W	30.0/762	Edge Clamp	3 ■
18215LG	LED	9W	30.0/762	Edge Clamp	5 ■
18253LG	LED	9W	30.0/762	Weighted Base	3 ■
18255BK	LED	9W	30.0/762	Weighted Base	5 ■
18255LG	LED	9W	30.0/762	Weighted Base	5 ■

ACCESSORIES

DESIGNATION

Rolling floor stands with casters and glides	50036
C Surface Mount Bracket	50005
B Wall Mount Bracket	50003LG
A Edge Mount Bracket	60001
10-diopter STAYS lens	50410
6-diopter STAYS lens	50406
4-diopter STAYS lens	50404