



# WAVE® LED Magnifiers

WAVE® LED Magnifiers - Luxo's newest, and most energy-efficient addition to its growing line of WAVE+Plus® Magnifiers. Now with two dimmable 6W LED lightsources which allow individual left/right lighting control and an auto shut-off feature to further ensure energy savings.



- Lighting: two dimmable 6W LEDs
- Left/right lighting controls
- 9/4 hour auto shut-off
- Magnification: 3.5- (1.88X) or 5-diopter (2.25X) lens
- 6.75" x 4.5" precision-ground white crown optical-quality glass lens
- 30" or 45" Heavy duty K-arm with 0.5" square steel tubing - 20 gauge CRS
- No knobs to tighten, nothing to adjust - a flexible, self-balancing shade and hands-free neck design allows the lamp head to be secured in any position
- ESD-Safe Magnifiers designed for use in static-sensitive environments are also available.
- Edge clamp or weighted base
- Colors: Light Grey or Black (ESD-Safe)
- 5 year warranty

## WAVE® LED Magnifiers

## CODES

## ESD-SAFE WAVE® LED MAGNIFIERS

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn.	Diopter	Colors
18904BK	LED	2x6	53.0	30.0/762	Weighted Base	2	3.5	■
18900BK	LED	2x6	13.0	45.0/1143	Edge Clamp	1	3.5	■
18902BK	LED	2x6	12.0	30.0/762	Edge Clamp	1	3.5	■
18910BK	LED	2x6	13.0	45.0/1143	Edge Clamp	1	5	■

## WAVE® LED MAGNIFIERS

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn.	Diopter	Colors
18845LG	LED	2x6	13.0	45.0/1143	Edge Clamp	1	3.5	■
18846LG	LED	2x6	12.0	30.0/762	Edge Clamp	1	3.5	■
18847LG	LED	2x6	53.0	30.0/762	Weighted Base	2	3.5	■
18945LG	LED	2x6	13.0	45.0/1143	Edge Clamp	1	5	■
18946LG	LED	2x6	12.0	30.0/762	Edge Clamp	1	5	■
18947LG	LED	2x6	53.0	30.0/762	Weighted Base	2	5	■

## ACCESSORIES

## DESIGNATION

Rolling floor stands with casters and glides	50036
C Surface Mount Bracket	50005
B Wall Mount Bracket	50003LG
A Edge Mount Bracket	60001
4-diopter STAYS lens	50404
6-diopter STAYS lens	50406
10-diopter STAYS lens	50410