

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [52484-1310](#)
Status: **Active**
Description: 2.0 W/B CONN. IDT REC. HSG ASSY

Documents:

3D Model	Product Specification PS-52484-012 (PDF)
Drawing (PDF)	Product Specification PS-52484-021 (PDF)
Product Specification PS-51090-003 (PDF)	Product Specification PS-52484-022 (PDF)
Product Specification PS-52478-001 (PDF)	Product Specification PS-53358-001 (PDF)
Product Specification PS-52478-002 (PDF)	Product Specification PS-55460-001 (PDF)
Product Specification PS-52484-009 (PDF)	Application Specification AS-52484-001 (PDF)
Product Specification PS-52484-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
TUV	R72090227
UL	E29179

General

Product Family	IDT and Solder Connectors
Series	52484
Crimp Quality Equipment	Yes
Product Name	Mi II™
UPC	800754238557

Physical

Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	726.900/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	0.85-1.05mm
Wire Size AWG	26, 28


Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Application Specification	AS-52484-001
---------------------------	--------------



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[52484Series](#)

Mates With

[51206](#) , [53313](#) , [55460](#) , [53358](#) , [53324](#) , [53325](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
IDT System Hand Tool	0621009900

Crimp Specification
Product Specification

CS-52484
PS-51090-003, PS-52478-001, PS-52478-002,
PS-52484-009, PS-52484-011, PS-52484-012,
PS-52484-021, PS-52484-022, PS-53358-001,
PS-55460-001, RPS-51090-002, RPS-51090-005,
RPS-51090-021, RPS-52484-002, RPS-52484-005,
RPS-52484-015, RPS-52484-016, RPS-52484-017,
RPS-52484-019, RPS-52484-020, RPS-52484-022,
RPS-52484-023, RPS-52484-024, RPS-52484-025,
RPS-52484-026, RPS-52969-004, RPS-52969-006,
RPS-53358-001, RPS-54111-005, RPS-55460-015
SD-52484-008

Sales Drawing

This document was generated on 12/17/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION