


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [50-57-9408](#)  
**Status:** **Active**  
**Overview:** [SL™ Modular Connectors](#)  
**Description:** [SL™ Crimp Housing, Single Row, Version G, Positive Latch, 8 Circuits](#)

**Documents:**

|  |  |
|--|--|
| <a href="#">3D Model</a>                             | <a href="#">Product Specification PS-71851 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                        | <a href="#">Test Summary TS-70058-001 (PDF)</a>      |
| <a href="#">Product Specification PS-70058 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Product Specification PS-70400 (PDF)</a> |  |



**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |  |
|----------------|--|
| Product Family | Crimp Housings                         |
| Series         | <a href="#">70066</a>                  |
| Application    | Signal, Wire-to-Board                  |
| Comments       | Version G                              |
| Overview       | <a href="#">SL™ Modular Connectors</a> |
| Product Name   | SL™                                    |
| UPC            | 800753577794                           |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 8               |
| Color - Resin                 | Black           |
| Flammability                  | 94V-0           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Keying to Mating Part         | Yes             |
| Lock to Mating Part           | Yes             |
| Material - Resin              | Polyester Alloy |
| Net Weight                    | 0.560/g         |
| Number of Rows                | 1               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 2.54mm          |
| Stackable                     | No              |
| Temperature Range - Operating | -40°C to +105°C |

**Electrical**


|                               |    |
|-------------------------------|----|
| Current - Maximum per Contact | 3A |
|-------------------------------|----|

**Material Info**

|                 |            |
|-----------------|------------|
| Old Part Number | 70066-0182 |
|-----------------|------------|

**Reference - Drawing Numbers**

|                       |                                   |
|-----------------------|-----------------------------------|
| Product Specification | PS-70058, PS-70400, PS-71851      |
| Sales Drawing         | SD-70066-0176-0199, SD-70066-0182 |
| Test Summary          | TS-70058-001                      |

|   |  |
|---|--|
| <b>EU RoHS</b><br><b>ELV and RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br><b>Contains SVHC: No</b><br><b>Low-Halogen Status</b><br><b>Not Low-Halogen</b> | <b>China RoHS</b><br> |
|---|--|

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[70066Series](#)

**Mates With**

[70018](#) , [70543](#) , [70545](#) , [70553](#) , [70555](#) , [70107](#) , [70541](#) , [70551](#) , [70634](#) , [74099](#)

**Use With**

SL™ Crimp Terminal [70058](#) , [71851](#)