

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0040](#)
Status: **Active**
Overview: Mini-Fit Jr.™ Power Connectors
Description: Mini-Fit® Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Reel

Documents:

Drawing (PDF)	Product Specification PS-52034-004 (PDF)
Product Specification PS-51010-005 (PDF)	Product Specification PS-5556-002 (PDF)
Product Specification PS-51010-006 (PDF)	Packaging Specification PK-5558-001 (PDF)
Product Specification PS-51096-001 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-52034-003 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0041 (Loose)
Product Name	Mini-Fit®
UPC	800753643239

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.123/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5558T
-----------------	-------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-51010-005, PS-51010-006, PS-51096-001, PS-52034-003, PS-52034-004, PS-5556-002, RPS-30067-002, RPS-42474-001
Sales Drawing	SD-5558****
Test Summary	TS-5556-002



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5558Series](#)

Mates With

[5556](#) Mini-Fit® Crimp Terminal

Use With

[5559](#) Mini-Fit Jr.™ Plug Housing, [30068](#) Mini-Fit® TPA Plug Housing, [42475](#) Mini-Fit® BMI Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900
FineAdjust™ Applicator for	0639023900

Insulation OD 1.40-1.70mm - 18-24 AWG T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24 AWG T2 Terminator™ for insulation OD 1.40-1.70mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only T2 Terminator™ for insulation OD 1.90-2.30mm - 18-24 AWG Extraction Tool FineAdjust™ Applicator for Insulation OD 2.50-2.95mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD 1.65-2.05mm - 18-24 AWG T2 Terminator™ for insulation OD 2.50-2.95mm - 18-24 AWG T2 Terminator™ for insulation OD 2.50-2.95mm optimized for 18 AWG only FineAdjust™ Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG T2 Terminator™ for insulation OD 2.30-2.60mm - 18-24 AWG Japan Description Hand Extraction Tool	 <u>0639102900</u> <u>0639123900</u> <u>0639024800</u> <u>0639115600</u> <u>0011030044</u> <u>0639002600</u> <u>0639002900</u> <u>0639102600</u> <u>0639124800</u> <u>0639015600</u> <u>0639024900</u> <u>0639124900</u>
	Product #
	0570316000

This document was generated on 12/17/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION