



FLIR IM75

Insulation & DMM Combo with METERLiNK®

The FLIR IM75 is both an advanced multifunction digital multimeter and premier handheld insulation tester for installation, troubleshooting and maintenance professionals. The IM75 includes several specialty insulation modes including: Polarization Index, Dielectric Absorption and Earth Bond Resistance. Insulation tests can be performed instantly, continuously and over a timed duration for in-depth assessment.

KEY FEATURES

- Advanced Insulation Modes: Insulation Resistance up to 20 GΩ, PI, DAR, Earth Bond Resistance
- Multiple ranges of resistance insulation test levels available via rotary switch: 50V, 100V, 250V, 500V, 1000V
- Multi-color LED indicator with Compare Mode makes pass/fail determinations easy and visible
- True RMS DMM measurements features reliable performance and 1000V range
- VFD Mode for superior accuracy on variable controlled drive equipment
- Remote viewing of real time readings on Android™ and iOS™ smartphones and tablets with METERLiNK® connectivity and free FLIR Tools Mobile app
- Transmit readings to METERLiNK-enabled FLIR thermal imaging cameras to document and analyze thermal changes during insulation measurements
- Extremely bright LED worklights in a flood pattern to illuminate test areas and targets
- Durable double-molded construction (IP54, 2m Drop Test)
- Ready for work with plenty of accessories: silicone CAT IV test leads with screw on silicone insulated alligator clips, and magnetic hanging strap

INCLUDES

- TA81 CAT IV Silicone Insulated Test Probes with screw on insulated alligator clips, TA50 Magnetic hanging strap, 6 x AAA batteries, User manual/CD



Specifications

TECHNICAL SUMMARY	MAX RANGE	BASIC ACCURACY
Insulation Resistance	4M to 20GΩ	±1.5%
Insulation Test Voltages	50, 100, 250, 500 and 1000V	±3.0%
DC Voltage	1000.0V	±0.1%
AC Voltage	1000.0V	±1.5%
VFD AC Voltage	1000.0V	±1.5%
Earth Bond Resistance	40Ω to 40KΩ	±1.5%
Capacitance	10 mF	±1.2%
Frequency (ACV)	40kHz	+/- 5 digits
Diode Test	2V	±1.5%
Continuity	400.0Ω	±0.5%
GENERAL INFORMATION		
IP Rating, Drop Test	IP 54, 2m (6.6')	
Category Rating	CAT III-1000V, CAT IV-600V	
Bluetooth Range	10m (32')	
Battery Type	6 x AAA	
Memory	99 internal storage locations	
Operating Temperature	32 to 122°F (0 to 50°C)	
Warranty	Limited Lifetime*	

* When registered within 60 days of purchase.



IM75 Features powerful worklights



Ordering Information

IM75... Insulation & DMM with VFD and METERLiNK™

IM75-NIST.....IM75 with Certificate of Traceability to NIST

Accessories

TA10.....Protective case for DM9x and IM7x Series

TA50.....Magnetic Hanging Strap

TA70.....CAT IV Insulated Alligator Clips

TA80.....CAT IV Silicone Test Leads

BOSTON

FLIR Systems, Inc.
9 Townsend West
Nashua, NH 03863
USA
PH: +1 266.477.3687

PORTLAND

Corporate Headquarters
FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
USA
PH: +1 866.477.3687

NETHERLANDS

FLIR Systems, Ltd.
Charles Petitweg 21
4847 NW Breda
Netherlands
PH: +31 (0) 765.41.85

CHINA - BEIJING

Room 502, West Wing,
Hanwei Building
No. 7 Guanghua Avenue
Chaoyang District,
Beijing 100004,
China
PH: +010.59797755

www.flir.com
NASDAQ: FLIR

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2014 FLIR Systems, Inc. All rights reserved. (Created 08/14)