

WAGO 224-112 Lighting Connector



2-conductor lighting connector Standard version Continuous service temperature 105°C

Product group	7 (Push Wire Conn.)
Cross section [mm ²]	1 - 2.5 mm ²
Cross section [AWG]	14 - 12 AWG
Wiring method	e
Connection method	CAGE CLAMP®CONNECTION
Number of strands	2
Cross section [mm ²]	0.5 - 2.5 mm ²
Cross section [AWG]	20 - 16 AWG
Wiring method	s + f-st
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	24 A
Weight	2.04 g
Color	white
Wiring type	Side-entry
No. of connection Points	3
No. of potentials	1
Height	15.5 mm
Height	0.61 in
Width	9.5 mm
Width	0.374 in
Depth	20.5 mm
Depth	0.807 in
Strip length from	9 mm
Strip length to	11 mm
Strip length	0.39 in