



# GFM20 -- Circuit Guard® GFCI Module



GFCI Module, manual set, yellow.

Product Specifications	
GFCI Product Type	
Amperage	20A
Color	 Yellow
Voltage	125V AC
Set Style	Manual
Device Style	Straight Blade
Trip Level	4-6 mA
Trip Time	0.025 seconds
Frequency	60Hz
Voltage Range	120V AC +10% -15%
Max Humidity	0.95
Operating Temp	Deg F -30 to 150 (Deg C -30 to 66)
UPC Number	78358552100
Weight in LBs	0.4