

Product availability: Stock - Normally stocked in distribution facility

Main

Commercial Status	Commercialised
Range of product	8501X
Relay type	Control
Product or component type	Relay
[In] rated current	5 A DC 10 A AC
Contacts type and composition	4 NO 4 standard contact cartridges
Control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Mounting support	Panel
Ambient air temperature for operation	-40...160 °F
Electrical connection	Screw clamp terminals
Product certifications	CE CSA UL listed
Operating time	16 ms drop-out 15 ms pick-up

Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
GTIN	00785901537052
Nbr. of units in pkg.	1
Package weight(Lbs)	2.16
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------