

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [16-06-0002](#)  
**Status:** **Active**  
**Overview:** Standard .093" Pin and Socket Connectors  
**Description:** 2.36mm Diameter, Standard .093" Pin and Male PC Board Terminal for Series 3099 Header Housing, Tin(Sn) Plated, Bag Packaged

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">1840</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Standard .093" Pin and Socket Connectors</a>
Product Name	Standard .093"
UPC	800754204873

**Physical**

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.158/g
Packaging Type	Bag
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	5A
Voltage - Maximum	250V

**Material Info**

Old Part Number	1840A2B
-----------------	---------

**Reference - Drawing Numbers**

Sales Drawing	SD-1840*
---------------	----------



*image - Reference only*

*Series*

**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Contains SVHC: No**  
**Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

1840Series

**Mates With**

1189 , 1381 , 2871 , 1433

**Use With**

[50-29-1031](#) , [50-29-1061](#) , [50-29-1041](#) ,  
[50-29-1409](#) , [50-29-1415](#) , [50-29-1412](#)