




# EGG.3P.306.PLW

(Not Recommended for New Design)

## MECHANICAL DETAILS

- Shell Style Model** EG\* : Fixed receptacle nut fixing with key
- Keying** User configurable, 1 of 11 key positions. Plug: male contacts; Receptacle: female contacts
- Housing Material** PSU (Polysulfone), gray
- Cable Fixing** 0 - 0 mm
- Variant 2** :

	A	L
Mm.	26.7	31.7
In.	1.05	1.25



## PERFORMANCE DETAIL

- Insert** 3P.306 : 6 Low Voltage plus 1 Ground
- Insulator**
- Specifications**
- Contact Type:** Special



## OTHER CHARACTERISTICS

- Shell Style/Model** Libellé
- F ret (min):** 100 N
- F ret (max):** 200 N
- Steam** 20 times
- IP Rating** 61

