



PAA.M0.7GL.AC65N

MECHANICAL DETAILS

Shell Style Model PA* : Straight plug with cable collet


Keying 2 keys (alpha=40; Plug: male contacts; Receptacle: female contacts)

Housing Material PSU (Polysulfone), gray

Cable Fixing 5.3 - 6.5 mm

Variant 2 N : Black collet nut

	A	L
Mm.	14	45
In.	0.55	1.77



PERFORMANCE DETAIL

Insert 1P.M07 : 7 Low Voltage

Insulator

Specifications

Contact Type: Solder

Max. Matings: 2000

Contact Dia.: 0.7 mm (0.0275in)

Bucket Dia.: 0.6 mm (0.024in)

Max. Solid 0.14 mm² (AWG 26)

Max. Stranded 0.14 mm² (AWG 26)

R (max): 6.5 mOhm



OTHER CHARACTERISTICS

Shell Style/Model Libellé

F ret (min): 50 N

F ret (max): 150 N

IP Rating 50

