



# PAG.M0.6NL.AC65N

## MECHANICAL DETAILS

**Shell Style Model** PA\* : Straight plug with cable collet


**Keying** 1 key (alpha=0; Plug: male contact; Receptacle: female contact)

**Housing Material** PSU (Polysulfone), black

**Cable Fixing** 5.3 - 6.5 mm

**Variant 2** N : Black collet nut

|     | A    | L    |
|-----|------|------|
| Mm. | 14   | 45   |
| In. | 0.55 | 1.77 |



## PERFORMANCE DETAIL

**Insert** 1P.M06 : 6 Low Voltage

**Insulator**

**Specifications**

**Contact Type:** Solder

**Max. Matings:** 2000

**Contact Dia.:** 0.7 mm (0.0275in)

**Bucket Dia.:** 0.6 mm (0.024in)

**Max. Solid** 0.14 mm<sup>2</sup> (AWG 26)

**Max. Stranded** 0.14 mm<sup>2</sup> (AWG 26)

**R (max):** 6.5 mOhm



## OTHER CHARACTERISTICS

**Shell Style/Model** Libellé

**F ret (min):** 50 N

**F ret (max):** 150 N

**IP Rating** 50

