



Kit P/N:GRM15-KIT-E [0402 Class 1 & 2 series]

Wallet

No.	Murata Global P/N	Size (EIA)	TC	WV	Cap.	Cap. Tol.	QTY
1	GRM1555C1HR50BA01	0402	C0G	50V	0.5pF	±0.1pF	20
2	GRM1555C1H1R0CA01	0402	C0G	50V	1.0pF	±0.25pF	20
3	GRM1555C1H1R2CA01	0402	C0G	50V	1.2pF	±0.25pF	20
4	GRM1555C1H1R5CA01	0402	C0G	50V	1.5pF	±0.25pF	20
5	GRM1555C1H1R8CA01	0402	C0G	50V	1.8pF	±0.25pF	20
6	GRM1555C1H2R2CA01	0402	C0G	50V	2.2pF	±0.25pF	20
7	GRM1555C1H2R7CA01	0402	C0G	50V	2.7pF	±0.25pF	20
8	GRM1555C1H3R3CA01	0402	C0G	50V	3.3pF	±0.25pF	20
9	GRM1555C1H3R9CA01	0402	C0G	50V	3.9pF	±0.25pF	20
10	GRM1555C1H4R7CA01	0402	C0G	50V	4.7pF	±0.25pF	20
11	GRM1555C1H5R6DA01	0402	C0G	50V	5.6pF	±0.5pF	20
12	GRM1555C1H6R8DA01	0402	C0G	50V	6.8pF	±0.5pF	20
13	GRM1555C1H8R2DA01	0402	C0G	50V	8.2pF	±0.5pF	20
14	GRM1555C1H100JA01	0402	C0G	50V	10pF	±5%	20
15	GRM1555C1H120JA01	0402	C0G	50V	12pF	±5%	20
16	GRM1555C1H150JA01	0402	C0G	50V	15pF	±5%	20
17	GRM1555C1H180JA01	0402	C0G	50V	18pF	±5%	20
18	GRM1555C1H220JA01	0402	C0G	50V	22pF	±5%	20
19	GRM1555C1H270JA01	0402	C0G	50V	27pF	±5%	20
20	GRM1555C1H330JA01	0402	C0G	50V	33pF	±5%	20
21	GRM1555C1H390JA01	0402	C0G	50V	39pF	±5%	20
22	GRM1555C1H470JA01	0402	C0G	50V	47pF	±5%	20
23	GRM1555C1H560JA01	0402	C0G	50V	56pF	±5%	20
24	GRM1555C1H680JA01	0402	C0G	50V	68pF	±5%	20
25	GRM1555C1H820JA01	0402	C0G	50V	82pF	±5%	20
26	GRM1555C1H101JA01	0402	C0G	50V	100pF	±5%	20
27	GRM1555C1H121JA01	0402	C0G	50V	120pF	±5%	20
28	GRM1555C1H151JA01	0402	C0G	50V	150pF	±5%	20
29	GRM1555C1H181JA01	0402	C0G	50V	180pF	±5%	20
30	GRM1555C1H221JA01	0402	C0G	50V	220pF	±5%	20
31	GRM1555C1H271JA01	0402	C0G	50V	270pF	±5%	20
32	GRM1555C1H331JA01	0402	C0G	50V	330pF	±5%	20
33	GRM1555C1H391JA01	0402	C0G	50V	390pF	±5%	20

No.	Murata Global P/N	Size (EIA)	TC	WV	Cap.	Cap. Tol.	QTY
34	GRM1555C1H471JA01	0402	C0G	50V	470pF	±5%	20
35	GRM1555C1H561JA01	0402	C0G	50V	560pF	±5%	20
36	GRM1555C1H681JA01	0402	C0G	50V	680pF	±5%	20
37	GRM1555C1H821JA01	0402	C0G	50V	820pF	±5%	20
38	GRM1555C1H102JA01	0402	C0G	50V	1000pF	±5%	20
39	GRM155R71H102KA01	0402	X7R	50V	1000pF	±10%	20
40	GRM155R71H222KA01	0402	X7R	50V	2200pF	±10%	20
41	GRM155R71H472KA01	0402	X7R	50V	4700pF	±10%	20
42	GRM155R71H103KA88	0402	X7R	50V	0.01µF	±10%	20
43	GRM155R71E223KA61	0402	X7R	25V	0.022µF	±10%	20
44	GRM155R71E473KA88	0402	X7R	25V	0.047µF	±10%	20
45	GRM155R61A104KA01	0402	X5R	10V	0.1µF	±10%	20
46	GRM155R61E104KA87	0402	X5R	25V	0.1µF	±10%	20
47	GRM155R71E104KE14	0402	X7R	25V	0.1µF	±10%	20
48	GRM155R71H104KE14	0402	X7R	50V	0.1µF	±10%	20
49	GRM155R61A224KE19	0402	X5R	10V	0.22µF	±10%	20
50	GRM155R71A224KE01	0402	X7R	10V	0.22µF	±10%	20
51	GRM155R71C224KA12	0402	X7R	16V	0.22µF	±10%	20
52	GRM155R61E224KE01	0402	X5R	25V	0.22µF	±10%	20
53	GRM155R6YA224KE01	0402	X5R	35V	0.22µF	±10%	20
54	GRM155R61A474KE15	0402	X5R	10V	0.47µF	±10%	20
55	GRM155R61C474KE01	0402	X5R	16V	0.47µF	±10%	20
56	GRM155R61E474KE01	0402	X5R	25V	0.47µF	±10%	20
57	GRM155R61A105KE01	0402	X5R	10V	1µF	±10%	20
58	GRM155R61C105KE01	0402	X5R	16V	1µF	±10%	20
59	GRM155R61E105KA12	0402	X5R	25V	1µF	±10%	20
60	GRM155R70J105KA12	0402	X7R	6.3V	1µF	±10%	20
61	GRM155R60J225ME95	0402	X5R	6.3V	2.2µF	±20%	20
62	GRM155R61A225KE95	0402	X5R	10V	2.2µF	±10%	20
63	GRM155R61C225ME11	0402	X5R	16V	2.2µF	±20%	20
64	GRM155R61E225KE11	0402	X5R	25V	2.2µF	±10%	20
65	GRM155R60J475ME47	0402	X5R	6.3V	4.7µF	±20%	20
66	GRM155R61A475MEAA	0402	X5R	10V	4.7µF	±20%	20
67	GRM155R60J106ME15	0402	X5R	6.3V	10µF	±20%	20

Effective October 2014

Subject to change without notice.

<http://www.murata.com/>

For the latest product information please check our website or contact your local Murata Sales Office

