

maxell

VHS







Standard Grade





- Maxell Standard Grade VHS videotape is specifically designed for the repeated recording and playback of everyday use
- Maxell Standard Grade VHS is formulated for extra sharp picture quality, brighter colors, fast, smooth cassette operation and maximum durability
- Great for recording in extended play modes (EP/LP)
- Available in 120 minute, 160 minute and 180 minute tape lengths





High Grade

- Maxell High Grade VHS videotape is designed for maximum quality reproduction of movies and any content you want to permanently preserve
- By taping on Maxell High Grade VHS Videotape in the EP (Extended Play) mode, you can achieve greater results in picture quality than recording in the SP (Standard Play) mode with a standard-grade tape, making it an excellent choice for taping long programs such as sporting events
- Available in 120 minute and 160 minute tape lengths



				
MODEL	HIGH GRADE T120	HIGH GRADE T120 3PK	HIGH GRADE T160	STD T120
Recording time	120 minutes	120 minutes	160 minutes	120 minutes
Item #:	224915	224939	224510	214016
Package Type:	Tab	Brick	Tab	Tab
Carton Inner/Master Qty:	10/50	10	10/50	10/50
UPC Codes:	Unit 0-25215-22491-1 Inner 300-25215-22491-2 Master 100-25215-22491-8	0-25215-22493-5 - 100-25215-22493-2	0-25215-22451-5 300-25215-22450-9 100-25215-22451-2	0-25215-21401-1 300-25215-21400-5 100-25215-21401-8
Dimensions: (LxWxH)	Unit 4 x 1 x 7.5 Inner 7.5 x 4 x 10.5 Master 23.25 x 12.25 x 9.125	4 x 3 x 7.5 - 16.5 x 8.5 x 9	4 x 1 x 7.5 7.5 x 4 x 10.5 23.25 x 12.25 x 9.125	4 x 1 x 7.5 7.5 x 4 x 10.5 23.25 x 12.25 x 9.125
Cube:	Unit 0.017 Inner 0.182 Master 1.19	0.052 - 0.73	0.017 0.182 1.19	0.017 0.182 1.19
Weight (lbs.):	Unit 0.55 Inner 5.56 Master 27.8	1.5 - 15.46	0.55 5.56 27.8	0.55 5.56 27.8

				
MODEL	STD T120 3PK	STD T120 4PK	STD T120 6PK	STD T120 8PK
Recording time	120 minutes	120 minutes	120 minutes	120 minutes
Item #:	214048	214049	215028	214150
Package Type:	Brick	Brick	Brick	Brick
Carton Inner/Master Qty:	10	10	10	5
UPC Codes:	Unit 0-25215-21403-5 Inner - Master 100-25215-21403-2	0-25215-21404-2 - 100-25215-21404-9	0-25215-21316-8 - 100-25215-21316-5	0-25215-21430-1 - 100-25215-21430-8
Dimensions: (LxWxH)	Unit 4 x 3 x 7.5 Inner - Master 16.5 x 8.5 x 9	4 x 4 x 7.5 - 21.125 x 8.375 x 8	6.25 x 4 x 7.5 - 20.875 x 12.75 x 8	4 x 8 x 7.5 - 21.125 x 8.75 x 8
Cube:	Unit 0.052 Inner - Master 0.73	0.069 - 0.819	0.109 - 1.232	0.139 - 0.861
Weight (lbs.):	Unit 1.5 Inner - Master 15.46	2 - 20.25	2.8 - 30.6	4.7 - 23.25

				
MODEL	STD T160	STD T160 3PK	STD T160 4PK	STD T180
Recording time	160 minutes	160 minutes	160 minutes	180 minutes
Item #:	213010	213030	213050	213027
Package Type:	Tab	Brick	Brick	Tab
Carton Inner/Master Qty:	10/50	10	6	10/50
UPC Codes:	Unit 0-25215-21301-4 Inner 300-25215-21301-5 Master 100-25215-21301-1	0-25215-21303-8 - 100-25215-21303-5	0-25215-21306-9 - 100-25215-92171-8	0-25215-21500-1 300-25215-21500-2 100-25215-21500-8
Dimensions: (LxWxH)	Unit 4 x 1 x 7.5 Inner 7.5 x 4 x 10.5 Master 23.25 x 12.25 x 9.125	4 x 3 x 7.5 - 16.5 x 8.5 x 9	4 x 4 x 7.5 - 12.75 x 8.625 x 8.125	4 x 1 x 7.5 7.5 x 4 x 10.5 23.25 x 12.25 x 9.125
Cube:	Unit 0.017 Inner 0.182 Master 1.19	0.052 - 0.73	0.069 - 0.517	0.017 0.182 1.19
Weight (lbs.):	Unit 0.55 Inner 5.56 Master 27.8	1.5 - 15.46	2.1 - 13	0.55 5.56 27.8

MAXELL LIMITED LIFETIME WARRANTY

Maxell warrants this product to be free from all defects for the lifetime of the product. This Warranty does not apply to normal wear or damage due to accident, abnormal use, misuse or neglect. This Warranty only applies to personal and individual use of the product and not for commercial, institutional or any other use. Any defective item will be replaced, at no charge, upon the reasonable confirmation by Maxell of its defective condition, if returned with proof of purchase to an authorized Maxell dealer or Maxell Corporation of America or directly to Maxell Warranty Replacement, P.O. Box 900, Fair Lawn, New Jersey 07410-0900. Neither Maxell nor any authorized Maxell dealer shall be liable for consequential damages arising from this Warranty, unless otherwise provided by law.



TECH SUPPORT
1.800.377.5887
techsupp@maxell.com



Maxell Corporation of America 22-08 Route 208, Fair Lawn, New Jersey, 07410
Maxell Canada 237 Romina Drive, Suite 200, Concord, ON Canada L4K 4V3
Maxell Europe Limited Whitebrook Park, Lower Cookham Road, Maidenhead Berkshire SL6 8YA, U.K.
Maxell Latin America Plaza Btsh - 50th St., Panama City, Rep. of Panama
www.maxell.com