



Ground Rod Clamps T&B Catalog Number:

UPC Number:
Status:
Description:

G5
78378680067
Active

Ground Rod Clamps Type G - Budget-Line, Rod Size 1/2 and 5/8, Wire Range 10 Sol. - 2 Str.

Features

Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.

Furnished with hex head bolts. Simplified, compact design makes lasting, trouble-free connection.

General

Style	Type G - Budget-Line
Material	Copper
Wire Range	10 Sol. - 2 Str.
Thread Size	3/8 - 16 UNC-2A
Ground Rod	1/2 and 5/8

Dimension Information

B (inches)	29/32
C (inches)	3/8
D (inches)	43/64
E (inches)	1/2
Rebar Size (inches)	#4

Packaging

T&B Inner Pack	1
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	10.25 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000478
T&B Instruction Sheets	wsd-000478
Overview	Available on Website

Notes

Add suffix P to Catalog number for tin-plated clamp.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com