

# Catamount®

**Spiral Wrap**

**T&B Catalog Number:**

SRPE-750-9-C

**UPC Number:**

72849409400

**Status:**

Active

**Description:**

Spiral Wrap Natural Polyethylene .750" OD, 100 Feet Per Roll

## Features

Perfect for protection of bundles from .062 to 7 inch diameters.

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation, and rigidity.

Available in three material types.

## General

Style	Reverse Cut
Material	Polyethylene
Color	Natural

## Dimension Information

Pitch (inches)	0.750
Nominal Wall Thickness (inches)	0.065
Max. Wire Bundle Diameter (inches)	5.000
Min. Wire Bundle Diameter (inches)	0.750
Outside Diameter (inches)	0.750

## Specifications

Flammability Rating	UL 94 HB
---------------------	----------

## Tooling

Application Tools	SR-100
-------------------	--------

## Packaging

T&B Order Multiple	1
Package in Units	1
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	7.4 lbs. Each

## Notes

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation and rigidity.

## Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

