

rotronic

Datenblatt - Fiche technique - Data sheet


11.02.8876



**ROLINE USB 3.0 Kabel, A ST – Micro B ST,
0,15m**

**ROLINE USB 3.0 Cable, A M – Micro B M,
0,15m**

**ROLINE USB 3.0 Cable,
USB Type A M – USB Type Micro B M, 0.15 m**




NOTES:

- 1.CABLE: UL20276 (28#*1P+EAM)*2C+28*1P+24#*2C+AEB OD:5.5mm
BLACK COLOR PVC JACKET
- 2.CONN: USB A/M INSULATION:BLUE, SHELL NICKEL-PLATED
CONTACT GOLD-PLATED 30U"
- 3.CONN: MICRO B/M INSULATION:BLUE, SHELL NICKEL-PLATED
CONTACT GOLD-PLATED 30U"
- 4.OUTER MOLD: PVC 45P BLACK

ELECTRICAL TEST:

- 1.100% TEST OPEN SHORT MIS-WIRE
- 2.INSULATION RESISTANCE:2M OHM MIN

WIRE ADDRESS



ITEM NO.	11.02.8876, 11.02.8877	Draw	F16	Date	2014.08.26	rotronic	D		
DESC.	ROLINE USB 3.0 Cable, A - Micro B, M/M, black	Check		Date			C		
	Unit (MM)	Approval		Date			B		
							VER. A	REVISE	Date