

# rotronic

Datenblatt - Fiche technique - Data sheet


11.02.8877



**ROLINE USB 3.0 Kabel, A ST – Micro B ST,  
3,0m**

**ROLINE USB 3.0 Cable, A M – Micro B M,  
3.0m**

**ROLINE USB 3.0 Cable,  
USB Type A M – USB Type Micro B M, 3.0 m**



A MALE

MICRO B MALE


NOTES:

- CABLE: UL20276 (28#\*1P+EAM)\*2C+28\*1P+24#\*2C+AEB OD:5.5mm  
BLACK COLOR PVC JACKET
- CONN: USB A/M INSULATION:BLUE, SHELL NICKEL-PLATED  
CONTACT GOLD-PLATED 30U"
- CONN: MICRO B/M INSULATION:BLUE, SHELL NICKEL-PLATED  
CONTACT GOLD-PLATED 30U"
- OUTER MOLD: PVC 45P BLACK

ELECTRICAL TEST:

- 100% TEST OPEN SHORT MIS-WIRE
- INSULATION RESISTANCE:2M OHM MIN

WIRE ADDRESS



ITEM NO.	11.02.8876, 11.02.8877	Draw	F16	Date	2014.08.26	<b>rotronic</b>	D		
DESC.	ROLINE USB 3.0 Cable, A - Micro B, M/M, black	Check		Date			C		
	Unit (MM)	Approval		Date			B		
							VER. A	REVISE	Date