


# rotronic

Datenblatt - Fiche technique - Data sheet


11.04.5553



**ROLINE Kabel DVI (18+1) ST – HDMI ST, 10 m**

**ROLINE Câble de raccordement pour écran  
DVI (18+1) M /HDMI M, 10 m**

**ROLINE DVI Cable, DVI (18+1) M – HDMI M, 10 m**



PINOUT:

P1 HDMI		P2 DVI-D(18P+1)	
RED CORE	2	3	GND
	1	2	WHITE
	3	1	WHITE/RED
GREEN CORE	5	11	GND
	4	10	WHITE
	6	9	WHITE/GREEN
BLUE CORE	8	19	GND
	7	18	WHITE
	9	17	WHITE/BLUE
BLACK CORE	11	22	GND
	10	23	WHITE
	12	24	WHITE/BLACK
	15	6	ORANGE
	16	7	YELLOW
	18	14	RED
	17	15	PURPLE
	19	16	WHITE
SHELL		DRAIN	SHELL

NOTES:

- 1) INSULATION RESISTANCE: 10M ohm (MIN) 300V/DC
- 2) CONTACT RESISTANCE: 5 ohm (MAX)
- 3) 360° copper foil and welding

4	OUTER JACKET PVC 45P BLACK
3	HDMI A TYPE PLUG TERMINAL PLATED GOLD 1U" SHELL PLATED NI
2	DVI 18P+1 M, BLACK, SOLDER TYPE
1	UL20276(28#1P+A+D)*4+28#1P+28#5C+A+B(128% AL-MG)+D OD:7.3MM BLACK 10M

11.04.5553

ROLINE DVI Cable, DVI - HDMI, M/M, 10m, black

**rotronic**

DIMENSIONS		TOLERANCE		CHKD.	CONF.				
0.00 TO 30.00mm		±0.10mm				DR. <i>san</i>	APPD.		
30.01 TO 80.00mm		±0.13mm							
80.01 TO 150.00mm		±0.15mm							
150.01mm		±0.20mm							
MATERIAL					SCALE	SHEET 1/1	UNIT <i>MM</i>	SIZE <i>A4</i>	REV. <i>A</i>
FINISH									