

rotronic

Datenblatt - Fiche technique - Data sheet


12.03.3140




**ROLINE Mini DisplayPort-VGA Adapter, v1.2,
Mini DP ST – VGA BU,**

**ROLINE Adaptateur Mini DisplayPort-VGA, v1.2,
Mini DP M – VGA F,**


**ROLINE Mini DisplayPort-VGA Adapter, v1.2,
Mini DP M – VGA F, white**



VGA Female



PIN Assignment



- ELECTRICAL TEST:**
- 1.100% OPEN SHORT & MIS WIRE TEST
 - 2.CONTACT RESISTANCE:2 OHM(MAX)
 - 3.INSULATION RESISTANCE:10M OHM(MIN)
 - 4.HI-POT TEST:DC 300V/10ms

NO	DESCRIPTION	Q'TY	UNIT
10	Mini DP M(MiniDP/VGA F PCB) ABS One-piece SHELL Apple WHITE PRINT: [] PT:COOL GRAY 8C W:5.0MM	1	pcs
9	Mini DP M(MiniDP/VGA F PCB) ABS One-piece SHELL WHITE	1	pcs
8	#4-40UNC H4.75*8.6MM PLATED: NICKEL NUT (NUT H=4.8MM)	2	pcs
7	φ 0.8 heat shrinkable TUBE BLACK 6mm*3pcs	0.018	m
6	Mini DisplayPort M TRANSPARENT COLOR PVC DUST COVER	1	pcs
5	VGA F(MiniDP/VGA F PCB) ABS One-piece SHELL WHITE	1	pcs
4	VGA F(MiniDP/VGA F PCB) ABS One-piece SHELL WHITE print: VGA (color: COOL GRAY 8C)	1	pcs
3	65P SNOWY WHITE PVC	4	g
2	empty PCB + SMT + PLATED: NICKEL	1	pcs
1	Mini DP M to M PLATED: NICKEL SNOWY WHITE 34AWG AL 0.4M 3 pair twist	1/2	pcs
	DESCRIPTION	Q'TY	UNIT

TOLERANCE INCHES M/M	
.X	.015 .30
.XX	.010 .10
.XXX	.005 .05

DRAWN BY	zheng
CHECK BY	
APPD BY	

Item No.:	12.03.3140
SCALE	NONE
UNIT	MM
DATE	13.03.15

REV. K	DRAWING NO.:
1/3	

rotronic

ROLINE Cable Adapter, MiniDP M to VGA F white color, v1.2