

# rotronic

Datenblatt - Fiche technique - Data sheet




12.03.3142



**ROLINE Mini DisplayPort-HDMI Adapter, v1.2,  
Mini DP ST – HDMI BU,**

**ROLINE Adaptateur Mini DisplayPort-HDMI, v1.2,  
Mini DP M – HDMI F,**

**ROLINE Mini DisplayPort-HDMI Adapter, v1.2,  
Mini DP M – HDMI F,**



**ELECTRICAL TEST:**  
 1. 100% OPEN SHORT & MTS WIRE TEST  
 2. CONTACT RESISTANCE: 2 OHM (MAX.)  
 3. INSULATION RESISTANCE: 10M OHM (MIN.)  
 4. HI-POT TEST: DC 300V/10ms

NO	DESCRIPTION	QTY	UNIT
10	W=20MM 25u DOUBLE CONDUCTIVE COPPER FOIL	0.09	m
9	Mini DP M(MiniDP/HDMI AF PCB) ABS One-piece WHITE	1	pcs
8	Mini DP M(MiniDP/HDMI AF PCB) ABS One-piece WHITE PRINT: [ ] (PT: COOL GRAY 8C W: 5.0MM)	1	pcs
7	φ 0.8 heat shrinkable TUBE BLACK 6mm*5pcs	0.03	m
6	Mini DisplayPort M TRANSPARENT COLOR PVC DUST COVER	1	pcs
5	HDMI A F ABS One-piece HEADER Apple SNOWY WHITE	1	pcs
4	HDMI A F ABS One-piece SHELL WHITE PRINT: DP 1.2 (neutral)	1	pcs
3	65P SNOWY WHITE PVC	9	g
2	empty PCB + SMT + PLATED: NICKEL	1	pcs
1	Mini DP M to M PLATED: NICKEL SNOWY WHITE 34AWG AL 0.4M 5 Pair twist	1/2	pcs
NO	DESCRIPTION	QTY	UNIT

TOLERANCE		M/M	
INCHES	M/M	INCHES	M/M
.X	-.015	.30	
.XX	-.010	.10	
.XXX	-.005	.05	

DRAWN BY	ZHOU	Item No.:	12.03.3142
CHECK BY		SCALE	NONE
APPD BY		UNIT	MM
		DATE	2014.04.01
		DRAWING NO.:	
		REV.	A
			1/3

**rotronic**

ROLINE Cable Adapter, Mini DP M to HDMI F white color, v1.2