

# SmartRack 12U Wall-Mount Rack Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: **SRW12U**



## Description

The SRW12U 12U Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 12U of standard 19" rackmount equipment. Supports up to 200 lbs of equipment. A sturdy wall-mount bracket allows the cabinet to quickly be hung on the wall.

## Features

- 12U wall-mounted enclosure
- Adjustable mounting depths up to 17" by 2 front vertical rackmount rails
- Ventilated front door and side panels for increased airflow
- Locking, reversible front door
- Locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

## Highlights

- Designed for IT and education environments where equipment needs to be secure and out of the way
- 12U with adjustable front vertical rackmount rails
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes.

## Applications

IT network environments with limited floor space and classrooms where equipment needs to be secure and out of the way of students.

## Package Includes

- SRW12U Wallmount Rack Enclosure
- (20) M6 screws
- (20) M6 cage nuts
- (20) M6 washers
- (2) Keys
- Owner's Manual

## Specifications

<b>SELECTOR</b>	
Selector Type	RACK EQUIPMENT
<b>General Info</b>	
Product Group	RACKS



TAA Compliant	No
<b>OVERVIEW</b>	
Style	Wall Mounted
Rack Type	Wall-Mount
<b>PHYSICAL</b>	
Installed Whole System Maximum Rack Depth (in.)	16.5
Installed Whole System Maximum Rack Depth (cm)	41.9
Installed Whole System Minimum Rack Depth (in.)	3
Rack Height (U Spaces)	12
Shipping Dimensions (hwd / in.)	27.95 x 26.38 x 20.67
Shipping Dimensions (hwd / cm)	71 x 67 x 52.5
Shipping Weight (lbs.)	55.1
Shipping Weight (kg)	25
Unit Dimensions (hwd / in.)	25.08 x 23.63 x 17.69
Unit Weight (lbs.)	48.5
Unit Weight (kg)	22
Unit Dimensions (cm)	63.7 x 60 x 44.93
Color	Black
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.7
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
<b>SPECIAL FEATURES</b>	
Grounding Lug	Front and Back door frames
<b>CERTIFICATIONS</b>	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.