


Part Number: 15121252

Type	Size	Rating	Description
LED	T6	12VDC	Midget Groove 6-chip Yellow



Colour	Voltage	Current (mA)	Intensity (mcd)
Yellow	12VDC	28 nom	110 nom

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Voltage tolerance ±10%
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The plastic (polycarbonate) has limited chemical resistance
- 7 RoHS & REACH SVHC compliant