



Based LED type	MultiLED
Size (inch)	T-1
Size (mm)	T3
Housing size	4.5x10mm
Base	BiPin 2.54
Chip number	4
Chip color	red
Wavelength (nm)	620
Op. voltage (V)	24
Rectifier	Protection Diode
AC current	-
DC current	12
Type I <sub>v</sub> DC current	19
Voltage tolerance (%)	10%
Op. temperature (°C)	-20°C...+60°C
Storage temperature (°C)	-25°C...+80°C

Drawn : DIL	Ch'd : DIL	Datasheet : 15010	Print date : 27/04/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :