

Hard Case® Pro Handhelds

No matter what a job demands in portable lighting, *Energizer* Hard Case Professional® flashlights can meet the challenge with their rugged dependability and innovative LED technology.

Energizer Hard Case Professional® LED Inspection Light



- High and low modes for brightness and runtime control
- Slim, compact design with one-handed easy operation
- Impact-resistant rubber head and tail with non-slip grip
- Shatterproof lens
- Water resistant
- Packed with two AAA *Energizer*® MAX® batteries

TUFPL22PH



Energizer Hard Case Professional® LED Task Light



- High and low modes for brightness and runtime control
- Compact, anti-roll design with push button switch
- Rugged construction
- Shatterproof lens
- Water resistant
- Packed with two AA *Energizer*® MAX® batteries

TUF2AAPE



Energizer Hard Case Professional® LED Project Light



- High and low modes for brightness and runtime control
- Bright white LEDs produce tight spot beam
- Push button switch
- Rugged and durable construction
- Shatterproof lens
- Water resistant
- Packed with four AA *Energizer*® MAX® batteries

TUF4AAPE



Energizer Hard Case Professional® LED Swivel Light



- Four light modes – high and low white beam, red for night vision and green for inspection work
- Flat base and swivel-head rotates 125°
- Sturdy clip attaches to belt or strap
- Water resistant
- Packed with two AA *Energizer*® MAX® batteries

TUF21PE

