





2AA ProPolymer® HAZ-LO Alkaline Battery-Powered Flashlight

FL 1 STANDARD	2AA PROPOLYMER HAZ-LO
	65 LUMENS
	24h
	96m
	2,300cd



Material/Lens Housing made from impact resistant engineering polymer. Facecap: Impact resistant engineering polymer overmolded onto polycarbonate lens. Available in yellow and black

Dims/Weight Length: 6.40 in. (16.26 cm) Major Diameter: 1.32 in. (3.35 cm) Body Diameter: 0.89 in. (2.26 cm) 3.6 oz (100 grams) with batteries

Light Source C4® LED technology, impervious to shock with a 50,000 hour lifetime

Switch Push-button tail switch. One handed momentary or constant “on” operation

Battery Two “AA” alkaline batteries (included)

- Features**
- Sealed construction; IPX7 rated design; waterproof to 1 meter for 30 minutes
 - 1 meter impact resistance tested
 - Push button tail switch for momentary and constant on operation
 - Features wrist lanyard connection and integrated pocket clip

Approvals C-SGS-US Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; T-Class: T4
(approved for use with Energizer E91, Duracell MN1500 and Rayovac NO.815)

MSHA Permissible Flashlight. Approval No. 20-A140002-0. Tested for Intrinsic Safety in Methane-Air mixtures only.
(approved for use with Energizer E91, Duracell MN1500 and Rayovac NO.815)

Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item		UPC	Part #
2AA ProPolymer HAZ-LO with alkaline batteries.	Yellow	080926-67101-0	67101
2AA ProPolymer HAZ-LO with alkaline batteries.	Black	080926-67100-3	67100





Hard hat and flashlight not included

Poly Mount Kit - universal mounting via slot attachment or self-adhesive mount

Includes adapters for mounting the 4AA ProPolymax®/ 3AA ProPolymer® HAZ-LO®, 2AA ProPolymer® Series or the PolyTac® LED Series

Clips onto hard hats or adheres to side of hard hat



Item		UPC	Part #
Polymount Kit		080926-68089-0	68089
Rubber Helmet Band		080926-99075-3	99075
Nylon holster		080926-85905-0	85905
Nylon holster (Deluxe)		080926-85909-8	85909
Safety Wand	Red	080926-74903-0	74903
Safety Wand	Yellow	080926-74904-7	74904
Safety Wand	Glow in the Dark	080926-74913-9	74913
Flip Filter	Red	080926-85115-3	85115
Flip Filter	Blue	080926-85116-0	85116
Flip Filter	Green	080926-85117-7	85117
Flip Filter	I/R	080926-74039-6	74039

