




**SPECIFICATION  
CONTROL DRAWING  
Crystal Resonator**

FREQUENCY
32.768000kHz



Holder Style	3x8 Cyl
Mode	Fundamental
Adjustment Tolerance	± 20PPM at 25°C
Temperature Stability	± -.042 PPM
Operating Temp. Range	-40°C to +85°C
Load Capacitance	12.5 pF
ESR	35K Max Ohm
Static Capacitance (C0)	Unspecified pF
Ageing	+/-5ppm 1st Year Max
Marking	Mark Std

Amdt Date	Change Note	AEL Code
	CSR Approved	<b>X32K768L102</b>
		<b>Issue Ref</b> A