

Classic Globe (GLS) Omni-Lamp 4.6W (40W) 3000K 470lm E27 Non-Dimmable 330 deg Beam Angle

Quick Order Code: 23-29-61 / Page: 1



This cutting edge A++, 4.6W retro-fit Integral LED Classic Globe (GLS) (frosted finish, large screw, white base) from the Omni-Lamp range delivers a warm white light and brightness, similar to a 40W filament bulb. It has the appearance, feel and weight of a traditional light bulb. Featuring a ceramic filament COB LED chip, which enables a super-wide 330 degree beam angle. Finished in an aluminium and plastic, thermally efficient body. Ideal for living rooms, hallways and kitchens.

Product Details

Partcode: ILA60E27O4.6N03KHEWA

Quick Order Code: 23-29-61

Range Name: Omni

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Classic Globe (GLS)

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: E27

Base Type: Edison screw

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Plastic, Aluminium, Glass, Nickel plated brass

Construction: Plastic and Aluminium heat sink, glass diffuser

Physical Data

Length: 106mm
Width: 60mm
Weight (Unpackaged Single Unit): 41g
Lamp or Luminaire Shape: Round
Lamp Fixing: Pendant

Electrical Data

Voltage Range: 220-240V
Power Consumption: 4.6 Watts
Driver included: Yes
Electric Current: AC
Ampage: 52.00mA
Frequency Range: 50/60 Hz
Power Factor: ≥ 0.40
Wattage Equivalent: 40 Watts
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 470lm
Lumens per Watt: 102.2lm/W
Beam Angle: 330°
Correlated Colour Temperature (CCT): 3,000k
Colour Temperature: Warm White
Colour Rendering Index (CRI): ≥ 80
LED Type: Filament ceramic COB chip
Instant on - Less than 1 second: Yes
Lifetime: 15,000 hrs
Switching Cycles: $>7,500$ X

Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788204237

Packaged Weight (Unit of 1): 99g

Length (unit of 1): 135mm

Width (unit of 1): 70mm

Depth (unit of 1): 70mm

Outer packaging info available on website

Product data last updated on: Tuesday, September 23, 2014 - 15:28