

## G9 1.5W (10W) 5000K 100lm Non-Dimmable Lamp

Quick Order Code: 56-50-55 / Page: 1



This 1.5W retro-fit Integral LED G9 delivers a cool white light and brightness, similar to a 10W halogen bulb. Ideal for living rooms, dining rooms and bedrooms, in classic or modern ceiling lamp fittings.

### Product Details

Partcode: ILG9C1.5N05KAAMA

Quick Order Code: 56-50-55

Range Name: Mensae

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: G9

Warranty: 3 Years

CE / RoHS: Yes

### Physical Data

Lamp Base: G9

Base Type: G9

Base Colour: Matt white

Globe Finish: Clear

**Physical Data**

Length: 47mm

Width: 14mm

Weight (Unpackaged Single Unit): 11g

Lamp or Luminaire Shape: Cylindrical

Lamp Fixing: Pendant

**Electrical Data**

Voltage Range: 220-240V

Power Consumption: 1.5 Watts

Driver included: Yes

Electric Current: AC

Ampage: 7.80mA

Frequency Range: 50/60 Hz

Power Factor:  $\geq 0.85$

Wattage Equivalent: 10 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

**Light Data**

Lumens: 100lm

Lumens per Watt: 67.0lm/W

Beam Angle: 145°

Correlated Colour Temperature (CCT): 5,000k

Colour Temperature: Cool White

Colour Rendering Index (CRI):  $\geq 80$

LED Manufacturer: ITC

LED Type: Surface mounted device (SMD)

Instant on - Less than 1 second: Yes

Lifetime: 25,000 hrs

Switching Cycles:  $>12,500$  X

### Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788204206

Packaged Weight (Unit of 1): 18g

Length (unit of 1): 60mm

Width (unit of 1): 35mm

Depth (unit of 1): 35mm

**Outer packaging info available on website**

*Product data last updated on: Tuesday, September 23, 2014 - 15:28*