

G4 1.5W (10W) 4000K 90lm Non-Dimmable 320 deg Beam Angle

Quick Order Code: 42-40-73 / Page: 1



This 1.5W retro-fit Integral LED G4 delivers a white light and brightness, similar to a 10W halogen bulb. Ideal for living rooms, dining rooms and bedrooms, in classic or modern ceiling lamp fittings.

Product Details

Partcode: ILG4C1.5N04KMAWA

Quick Order Code: 42-40-73

Range Name: Dorado

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: G4

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: G4

Base Type: G4

Base Colour: Matt white

Globe Finish: Clear

Material: Copper Heat Sink, plastic housing

Physical Data

Length: 23mm

Width: 10mm

Weight (Unpackaged Single Unit): 3g

Lamp or Luminaire Shape: Cylindrical

Lamp Fixing: Pendant

Electrical Data

Voltage Range: 12V

Power Consumption: 1.5 Watts

Driver included: Yes

Electric Current: AC/DC

Ampage: 90.00mA

Frequency Range: 50/60 Hz

Power Factor: ≥ 0.70

Wattage Equivalent: 10 Watts

Dimming: Non-dimmable

EN: EN 61547:2009

Light Data

Lumens: 90lm

Lumens per Watt: 60.0lm/W

Beam Angle: 320°

Correlated Colour Temperature (CCT): 4,000k

Colour Temperature: White

Colour Rendering Index (CRI): ≥ 80

LED Manufacturer: Samsung

LED Type: Surface mounted device (SMD)

LED Size: 2323

Instant on - Less than 1 second: Yes

Lifetime: 25,000 hrs

Switching Cycles: $>12,500$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -30 degrees

Maximum Operating Temperature: 45 degrees

IP (Ingress Protection) Rating: IP40

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788206262

Packaged Weight (Unit of 1): 4g

Length (unit of 1): 36mm

Width (unit of 1): 15mm

Depth (unit of 1): 15mm

Outer packaging info available on website

Product data last updated on: Tuesday, September 23, 2014 - 15:31